


Glass Select Fire™

Both the GSF-045 and GSF-670 glass kilns are equipped with the Glass Select Fire™ controller. It's easy to program and includes many innovative features. You can even change the program after it has started to better suit your needs!

- 
- ◆ **LED Display**
 - ◆ **MENU** allows access to advanced programming features
 - ◆ If an error is made the programmer can press **BACK** to input the correct data
 - ◆ The **ANNEAL** key is pressed when the glass has attained the desired heatwork and the artist wishes to begin the annealing process
 - ◆ **ADD TIME** key adds time to the final heating segment in increments of 5 minutes during the firing
 - ◆ **ADD TEMP** adds 5 degrees F of heat to the final heating segment
 - ◆ The **VIEW** key will display the current segment of the firing program
 - ◆ **RAMP HOLD** allows the professional to construct and store their own specialized firing programs
 - ◆ The Glass Select Fire™ can be programmed in **FAHRENHEIT or CENTIGRADE**
 - ◆ The **REVIEW** key displays the program that is currently loaded
 - ◆ The **START** key begins the program
 - ◆ The **STOP** key will stop the program at any point in the firing
 - ◆ The **GLASS FIRE** key accesses preset fusing, slumping, and tack fusing programs with choices of varying firing speeds
 - ◆ The **CYCLE** key is used in conjunction with the Glass Fire key to choose various options
 - ◆ For quick access to stored Ramp Hold programs simply press the **RECALL** key